



Combination spanner, long version, Width across flats: 15mm



Order data

Order number	614900 15
GTIN	4045197442093
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Width across flats	15 mm
Spanner length L	230 mm
maximum jaw height h ₁	7 mm
Width across flats	metric
maximum ring height h _{2 max}	11 mm
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner

