



Double-ended ring spanner, deeply cranked, Width across flats: 21X24mm



Order data

| | |
|--------------|---------------|
| Order number | 615000 21X24 |
| GTIN | 4018754021048 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile.

Advantage:

AS-Drive profile:

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 615600

Technical description

| | |
|------------------------------------|--------|
| Spanner length L | 330 mm |
| maximum ring $\varnothing D_1$ max | 32 mm |
| Width across flats 2 | 24 mm |

| | |
|------------------------------------|---------|
| Width across flats 1 | 21 mm |
| maximum ring $\varnothing D_2$ max | 35 mm |
| Width across flats | metric |
| Type of product | Spanner |