

**Combination spanner, long version, Width across flats: 32mm****Order data**

Order number	614900 32
GTIN	4045197442208
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum jaw height h1	14 mm
Width across flats	32 mm
Spanner length L	444 mm
Width across flats	metric
maximum ring height h _{2 max}	21 mm
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner

