



## Double-ended ring spanner, deeply cranked, Width across flats: 24X27mm



### Order data

Order number	615000 24X27
GTIN	4018754021079
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile.

#### Advantage:

##### AS-Drive profile:

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 615600

### Technical description

maximum ring $\varnothing D_2$ max	40 mm
maximum ring $\varnothing D_1$ max	36 mm
Width across flats 2	27 mm

Spanner length L	330 mm
Width across flats 1	24 mm
Width across flats	metric
Type of product	Spanner