



## Double-ended ring spanner set, deeply cranked, Number of keys: 12



### Order data

Order number	615500 12
GTIN	4018754058457
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS drive** profile.

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

#### Supplied with:

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34

### Technical description

Number of keys	12
Width across flats	metric
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome plated (non-flaking)

Type of product	Spanner
-----------------	---------

## Accessories

Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615000 10X11
Double-ended ring spanner, deeply cranked Width across flats 18X19 mm	615000 18X19
Double-ended ring spanner, deeply cranked Width across flats 27X32 mm	615000 27X32
Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615000 16X17
Double-ended ring spanner, deeply cranked Width across flats 21X23 mm	615000 21X23
Double-ended ring spanner, deeply cranked Width across flats 20X22 mm	615000 20X22
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615000 14X15
Double-ended ring spanner, deeply cranked Width across flats 24X26 mm	615000 24X26
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615000 6X7
Double-ended ring spanner, deeply cranked Width across flats 30X34 mm	615000 30X34
Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615000 8X9
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615000 12X13