



Double-ended ring spanner, deeply cranked, Width across flats: 17X19mm



Order data

Order number	615000 17X19
GTIN	4018754020966
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile.

Advantage:

AS-Drive profile:

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 615600

Technical description

maximum ring $\varnothing D_1$ max	28 mm
Width across flats 2	19 mm
maximum ring $\varnothing D_2$ max	29 mm

Width across flats 1	17 mm
Spanner length L	270 mm
Width across flats	metric
Type of product	Spanner