



## Double-ended ring spanner set, deeply cranked, Number of keys: 13



### Order data

Order number	615500 13
GTIN	4018754058464
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS drive** profile.

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

#### Supplied with:

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34; 36×41

### Technical description

Number of keys	13
Width across flats	metric
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome plated (non-flaking)

Type of product

Spanner

**Accessories**

Double-ended ring spanner, deeply cranked Width across flats 14X15 mm

615000 14X15

Double-ended ring spanner, deeply cranked Width across flats 30X34 mm

615000 30X34

Double-ended ring spanner, deeply cranked Width across flats 10X11 mm

615000 10X11

Double-ended ring spanner, deeply cranked Width across flats 18X19 mm

615000 18X19

Double-ended ring spanner, deeply cranked Width across flats 6X7 mm

615000 6X7

Double-ended ring spanner, deeply cranked Width across flats 27X32 mm

615000 27X32

Double-ended ring spanner, deeply cranked Width across flats 20X22 mm

615000 20X22

Double-ended ring spanner, deeply cranked Width across flats 16X17 mm

615000 16X17

Double-ended ring spanner, deeply cranked Width across flats 24X26 mm

615000 24X26

Double-ended ring spanner, deeply cranked Width across flats 8X9 mm

615000 8X9

Double-ended ring spanner, deeply cranked Width across flats 12X13 mm

615000 12X13

Double-ended ring spanner, deeply cranked Width across flats 36X41 mm

615000 36X41

Double-ended ring spanner, deeply cranked Width across flats 21X23 mm

615000 21X23