



Bi-hexagon socket deep, 1/2 inch, Width across flats: 19mm



Order data

Order number	642500 19
GTIN	4018754005635
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish. Bi-hexagon with **AS drive** profile.

Standard:

DIN 3124-L

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 642529

Technical description

Length	83 mm
Width across flats	19 mm
Ø drive output end	26.2 mm
Square drive	1/2 in
Standard	ASME B 107.5M
Standard	DIN EN 3709

Standard	DIN 3124
Standard	DIN EN 3710
Standard	ISO 2725-1
Drive profile	Bi-hex socket
Material	Chrome alloy steel
Surface	chrome-plated
with AS Drive profile.	yes
Type of product	Socket insert