



## Bi-hexagon spark plug socket, 1/2 inch, Width across flats: 20,8mm



### Order data

Order number	642450 20,8
GTIN	4018754005734
Item class	63A

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. With rubber insert for holding the spark plug.

Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

#### Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

### Technical description

Drive profile	Bi-hex socket
Length	83 mm
Retention mechanism for spark plugs	Rubber retainer
Width across flats	20.8 mm
Ø drive output end	27.7 mm
Width across flats	13/16 in
Square drive	1/2 in
Material	Chrome alloy steel
Surface	chromium-plated over nickel

Type of product

Socket insert