



Bi-hexagon socket deep, 1/2 inch, Width across flats: 22mm



Order data

| | |
|--------------|---------------|
| Order number | 642500 22 |
| GTIN | 4018754005659 |
| Item class | 63A |

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish. Bi-hexagon with **AS drive** profile.

Standard:

DIN 3124-L

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 642529

Technical description

| | |
|--------------------|---------------|
| Length | 83 mm |
| Width across flats | 22 mm |
| Ø drive output end | 29.7 mm |
| Square drive | 1/2 in |
| Standard | ASME B 107.5M |
| Standard | DIN EN 3709 |

| | |
|------------------------|--------------------|
| Standard | DIN 3124 |
| Standard | DIN EN 3710 |
| Standard | ISO 2725-1 |
| Drive profile | Bi-hex socket |
| Material | Chrome alloy steel |
| Surface | chrome-plated |
| with AS Drive profile. | yes |
| Type of product | Socket insert |