

**Garant****Circular saw blade, wood, alternating teeth medium, Blade Ø D: 400mm****Order data**

Order number	584035 400
GTIN	4045197220806
Item class	51S

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

For circular, cross-cut, compound, and mitre saws.

Type UW for **board materials, veneered or plastic coated on one side**, veneer packs longitudinally, hard paper and hard fabric.

**Note:**

**Further circular saw blades can be found in Group 17.**

**Technical description**

Blade Ø D	400 mm
Bore Ø	30 mm
Number of teeth	60
Width of cut B	3.5 mm

Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade