

Garant**Circular saw blade, wood, alternating teeth medium, Blade Ø D: 300mm****Order data**

Order number	584035 300
GTIN	4045197220776
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Type UW for **board materials, veneered or plastic coated on one side**, veneer packs longitudinally, hard paper and hard fabric.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Bore Ø	30 mm
Blade Ø D	300 mm
Number of teeth	48
Width of cut B	3.2 mm

Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade