



## Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 19X22mm



### Order data

Order number	615900 19X22
GTIN	4045197385499
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

**Standard:**

**DIN 838 / ISO 3318**

**Material:**

Chrome vanadium steel, phosphated.

### Technical description

Width across flats 2	22 mm
maximum ring $\varnothing D_1$ max	29 mm
maximum ring $\varnothing D_2$ max	34 mm
Width across flats 1	19 mm
Spanner length L	318 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

