



Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 27X32mm



Order data

Order number	615900 27X32
GTIN	4045197385550
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum ring $\varnothing D_1$ max	40 mm
maximum ring $\varnothing D_2$ max	48 mm
Spanner length L	360 mm
Width across flats 1	27 mm
Width across flats 2	32 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

