

ARIANA**High pressure nozzle 1/8 inch external thread, Tube length: 31mm****Order data**

Order number	084435 31
GTIN	4037728217331
Item class	08J

Description**Version:**

High-pressure nozzle for up to 90 bar High-pressure cooling and pivoting range of 70°, up to 110°. Housing of high quality plastic granules.

- **For space-saving insertion in the existing hose system.**
- **Nozzle with 360° rotation.**
- **Various pipe lengths.**

Application:

For retrofitting into the existing system. Quick cutting when machining at high speeds thanks to high-pressure cooling.

Technical description

Tube length	31 mm
Internal Ø nozzle	2 mm
Connection thread	1/8 in
Type of product	Cooling system

