

Ansell**Disposable glove set, MicroFlex® 93-260, Glove size: 10****Order data**

Order number	094724 10
GTIN	076490453503
Item class	04P

Description**Version:**

Disposable glove set **in dispenser**. Category III. Powder-free. MicroFlex® 93-260. 3-layer design for good chemical resistance, including resistance to acids, solvents and alkalis. Structured fingertips. Long cuff and low AQL value of 0.65 (EN 374-2) for reliable protection against hazardous substances.

Standard:

EN 374

Technical description

Glove size	10
Series	MicroFlex®
Protection category	Category III
Type of glove	Disposable glove
Glove characteristics	Silicone-free
Glove characteristics	free of latex

Glove characteristics	Suitable for allergy sufferers
EN 374	Type A (JKLOPST)
Resistance to chemicals	JKLOPST
EN 388	2000X
Material	Neoprene, nitrile
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
Backing material	Neoprene, nitrile
Coating	Neoprene, nitrile
Thickness	0.2 mm
Length	285 mm
Contents	50
Weight	8.1 g
Colour	green
Application range	Precision
AQL	0.65
Application	disposable
Type of product	Disposable glove