

**ARIANA****High pressure nozzle 1/4 inch external thread, Tube length: 31mm**

## Order data

Order number	084436 31
GTIN	4037728217492
Item class	08J

## Description

### Version:

**High-pressure nozzle for up to 90 bar** High-pressure cooling and pivoting range of 70°, up to 110°. Housing of high quality plastic granules.

- **For space-saving insertion in the existing hose system.**
- **Nozzle with 360° rotation.**
- **Various pipe lengths.**

### Application:

**For retrofitting** into the existing system. Quick cutting when machining at high speeds thanks to high-pressure cooling.

## Technical description

Tube length	31 mm
Internal Ø nozzle	2 mm
Connection thread	1/4 in
Type of product	Cooling system

