

ejendals

Pair of chemical protective gloves Tegera® 12930, Glove size: 8



Order data

Order number	094795 8
GTIN	7392626068391
Item class	04R

Description

Version:

Category III safety gloves.

Tegera® 12930. Chemical protection gloves of PVC for rough work. Resistant to oils and greases. Granulated in hand area for good slip resistance. Particularly hard-wearing, even in dirty and greasy areas.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. EN 374:2016: Type B (KLMPT)

Technical description

Glove size	8
Protection category	Category III
Type of glove	Chemicals protection gloves
Contents	12
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374

EN 374:2016	Type B (KLMPT)
Resistance to chemicals	KLMPT
EN 388:2016	4131X
EN 407	X2XXXX
Material	PVC
Backing material	PVC
AQL	0.3
Application range	All-round
Length	300 mm
Colour	black / blue
Application	reusable
Contact heat up to	250 °C
Type of product	Chemicals protection gloves