

Garant

Double-ended ring spanner, deeply cranked, Width across flats: 18X19 mm



Order data

| | |
|--------------|---------------|
| Order number | 615700 18X19 |
| GTIN | 4045197160720 |
| Item class | 61A |

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **AS drive** profile.

Advantage:

AS drive profile:

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. All GARANT and STAHLWILLE deep cranked double-ended ring spanners are equipped with this profile – recognisable by the **AS drive** mark.

Spanner length L: 275 mm

maximum ring $\varnothing D_1$ max: 28 mm

maximum ring $\varnothing D_2$ max: 29 mm

Technical description

| | |
|------------------------------------|-------|
| maximum ring $\varnothing D_2$ max | 29 mm |
|------------------------------------|-------|

| | |
|------------------------------------|---------|
| Width across flats 1 | 18 mm |
| Spanner length L | 275 mm |
| maximum ring $\varnothing D_1$ max | 28 mm |
| Width across flats 2 | 19 mm |
| Width across flats | metric |
| Type of product | Spanner |