

Mitutoyo**External micrometer Inch graduations, Measuring range: 1-2****Order data**

Order number	420600 1-2
GTIN	4946368003566
Item class	44A

Description**Version:**

Barrel non-reflecting chrome plated.

Precision lapped, carbide-tipped measuring faces. Hardened and ground measuring spindle. Locking by locking lever. With ratchet. Precision engraved black divisions and numerals.

Supplied with:

From size 1-2 including 1 setting standard.

Technical description

Barrel Ø	18 mm
Type of measurement face	carbide tipped
Calibration	B2
Spindle Ø	6.35 mm
Scale divisions	0.0001 in
Measuring range	1 - 2 in
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Micrometer setting standard overall length 1	421150 1
--	----------