

**Mitutoyo**
**External micrometer Inch graduations, Measuring range: 0-1**

**Order data**

Order number	420600 0-1
GTIN	4946368003559
Item class	44A

**Description**
**Version:**

Barrel non-reflecting chrome plated.

**Precision lapped, carbide-tipped measuring faces.** Hardened and ground measuring spindle. Locking by locking lever. With ratchet. Precision engraved black divisions and numerals.

**Supplied with:**

From size 1-2 including 1 setting standard.

**Technical description**

Spindle Ø	6.35 mm
Calibration	B1
Type of measurement face	carbide tipped
Barrel Ø	18 mm
Scale divisions	0.0001 in
Measuring range	0 - 1 in
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

Calibration External micrometer without setting dimension  
maximum measuring range 25 mm

022000 25

DAkkS calibration External micrometer without setting  
dimension maximum measuring range 100 mm

022010 100