



## Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 8X10mm



### Order data

Order number	615950 8X10
GTIN	4045197441713
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

**Standard:**

**DIN 838 / ISO 3318**

**Material:**

Chrome vanadium steel, chrome-plated.

### Technical description

Width across flats 1	8 mm
maximum ring $\varnothing D_2$ max	16 mm
maximum ring $\varnothing D_1$ max	14 mm
Spanner length L	182 mm
Width across flats 2	10 mm
Width across flats	metric
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

