



## Dynafor LLZ2 load dynamometer, maximum weighing range: 6,3 t



### Order data

Order number	086049 6,3
GTIN	3600232609094
Item class	08Y

### Description

#### Version:

Dynafor LLZ2 versatile robust and reliable load dynamometer. Integral LCD display with good legibility. Display strengthened for protection.

- **Bevelled edges to minimise the risk of becoming entangled when lifting.**
- **Safety factor > 4.**
- **Precision and traceability certified by the adjustment certificate. Accuracy 0.3%. Can be recalibrated.**
- **Can be used in all positions. Protection class IP65: Suitable for use in the open air. Conform to CE and the Machines Directive 2006/42/EC.**
- **Temperature range -20°C to +50°C.**

#### Application:

For measuring tensile forces (N) and suspended masses (kg).

#### Supplied with:

Includes batteries (2× AAA), calibration certificate, transport case.

IP Index of Protection: IP 65

Packaging: Carrying case

Test certificate: Manufacturer's test certificate

smallest weighing range: 10 kg

Body width: 121.5 mm

Body depth: 22 mm

Body height: 236 mm

---

## Technical description

Body width	121.5 mm
maximum weighing range	6300 kg
Body depth	22 mm
Body height	236 mm
smallest weighing range	10 kg
Article no of the battery / rechargeable battery fitted	081556 LR3
Number of batteries contained	2
IP Index of Protection	IP 65
Packaging	Carrying case
Test certificate	Manufacturer's test certificate