



Dynafor LLZ2 load dynamometer, maximum weighing range: 12,5 t



Order data

Order number	086049 12,5
GTIN	3600232609193
Item class	08Y

Description

Version:

Dynafor LLZ2 versatile robust and reliable load dynamometer. Integral LCD display with good legibility. Display strengthened for protection.

- **Bevelled edges to minimise the risk of becoming entangled when lifting.**
- **Safety factor > 4.**
- **Precision and traceability certified by the adjustment certificate. Accuracy 0.3%. Can be recalibrated.**
- **Can be used in all positions. Protection class IP65: Suitable for use in the open air. Conform to CE and the Machines Directive 2006/42/EC.**
- **Temperature range -20°C to +50°C.**

Application:

For measuring tensile forces (N) and suspended masses (kg).

Supplied with:

Includes batteries (2× AAA), calibration certificate, transport case.

IP Index of Protection: IP 65

Packaging: Carrying case

Test certificate: Manufacturer's test certificate

smallest weighing range: 20 kg

Body width: 120.5 mm

Body depth: 45 mm

Body height: 277 mm

Technical description

Body width	120.5 mm
maximum weighing range	12500 kg
Body height	277 mm
Body depth	45 mm
smallest weighing range	20 kg
Article no of the battery / rechargeable battery fitted	081556 LR3
Number of batteries contained	2
IP Index of Protection	IP 65
Packaging	Carrying case
Test certificate	Manufacturer's test certificate