

**VBW****Corner pipe wrench with S-form jaws, Pipe Ø: 1.1/2in****Order data**

Order number	810740 1.1/2
GTIN	4005887265401
Item class	83E

**Description****Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

**VBW** with **S-form jaws** for 3-point pipe support.

**Material:**

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

**Technical description**

overall length	440 mm
Pipe Ø	1.1/2 in
Jaw capacity	68 mm
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

