

VBW**Corner pipe wrench with S-form jaws, Pipe Ø: 2in****Order data**

| | |
|--------------|---------------|
| Order number | 810740 2 |
| GTIN | 4005887265500 |
| Item class | 83E |

Description**Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

VBW with **S-form jaws** for 3-point pipe support.

Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

Technical description

| | |
|---------------------------|-----------------------------------|
| Pipe Ø | 2 in |
| Jaw capacity | 85 mm |
| overall length | 560 mm |
| Jaw angle | 45 degrees |
| Manufacturing process | forged throughout |
| Hardened and tempered jaw | induction hardened |
| Material of pliers | Chrome vanadium steel |
| S-jaw | yes |
| Swedish profile | yes |
| Type of product | Pipe wrench and water pump pliers |

