



Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 41X46mm



Order data

Order number	615900 41X46
GTIN	4045197385604
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

Spanner length L	475 mm
Width across flats 2	46 mm
Width across flats 1	41 mm
maximum ring $\varnothing D_2$ max	67 mm
maximum ring $\varnothing D_1$ max	60 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

