

Garant
Double-ended ring spanner set, deeply cranked, Number of keys: 8

Order data

Order number	615710 8
GTIN	4045197160874
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw widths.

GARANT – With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **AS drive** profile.

Standard:

DIN 838 / ISO 3318

Material:

GARANT – Chrome alloy steel; chrome-plated (non-flaking), smoothed finish.

Content:

1 each spanner No. 615700 / 615000 / 615900 / 615950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Supplied with:

1 each double ended ring spanner No. 615700 / 615000 / 615900 / 615950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Technical description

Number of keys	8
Width across flats	metric
Ring setting	75 degrees

Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome plated (non-flaking)
Type of product	Spanner

Accessories

Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615700 8X9
Double-ended ring spanner, deeply cranked Width across flats 18X21 mm	615700 18X21
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615700 14X15
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615700 10X11
Double-ended ring spanner, deeply cranked Width across flats 19X22 mm	615700 19X22
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615700 12X13
Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615700 16X17
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615700 6X7