

HOLEX**Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 24X27mm****Order data**

Order number	615900 24X27
GTIN	4045197385529
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum ring $\varnothing D_2$ max	40 mm
Width across flats 2	27 mm
maximum ring $\varnothing D_1$ max	36 mm
Spanner length L	337 mm
Width across flats 1	24 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

