

Arbor press, Type: 0



Order data

Order number	086790 0
GTIN	
Item class	08V

Description

Version:

Sturdy, hollow cast body of special cast iron with large base. Base with mounting holes for attaching to the support (workbench / subframe No. 086795). Rack and pinion slide ram of wear-resistant steel for the heaviest duties. Precise operation due to hardened and polished rack and pinion slide ram with long guides. Rotating table with four different recesses for the support of different workpieces. Slide ram actuation by lever arm.

Application:

For pressing in and pressing out sleeves, ball bearings, arbors, pins, bolts etc. Also for broaching work as well as use of simple cutting and stamping tools.

Colour:

Light grey RAL 7035.

Technical description

Slit width of the support table	10/15/20/25 mm
Footprint depth	195 mm
maximum slide ram stroke	110 mm
Weight	11 kg

Footprint width	130 mm
maximum pressure delivery	5.11 kN
Cast body height	260 mm
Slide bar Ø	28 mm
Throat to slide ram centre	100 mm
for workpiece Ø up to	180 mm
Type	0
Type of product	Arbor press