

GECHTER**Hand lever toggle press, Type: 5****Order data**

Order number	086760 5
GTIN	2050001743923
Item class	08V

Description**Version:**

Sturdy, hollow cast body with large base. Base with 4 holes for attachment to workbench etc. The press tool carriage runs without play on dovetail guides and is adjustable for height. Additionally the press stroke (ram stroke) can also be set by an adjusting screw to give the desired vertical lift. The table has a 10 mm T-slot for attaching clamps.

Application:

For embossing, riveting, upsetting, and punching as well as for bending, compressing, and pressing in bushes etc.

Colour:

Light grey RAL 7035.

Note:

Hand lever presses with air support available in the online shop under No. 086761.

Force for short stroke: 14 kN

Stroke length long: 0 - 40 mm

Throat: 90 mm

Installation height: 70 - 195 mm

Mounting hole in the slide ram: 10 H 7 mm

Table width: 180 mm

Technical description

Footprint width	180 mm
Stroke length long	0 - 40 mm
Weight	20 kg
Mounting hole in the slide ram	10 H 7 mm
Throat	90 mm
Height without hand lever	420 mm
Footprint depth	240 mm
T-slot to DIN 650	1 pc. size 10
Force for short stroke	14 kN
Type	5
Table depth	110 mm
Table width	180 mm
Installation height	70 - 195 mm
Type of product	Toggle lever press