

GECHTER**Hand lever toggle press, Type: 12****Order data**

Order number	086760 12
GTIN	2050001742469
Item class	08V

Description**Version:**

Sturdy, hollow cast body with large base. Base with 4 holes for attachment to workbench etc. The press tool carriage runs without play on dovetail guides and is adjustable for height. Additionally the press stroke (ram stroke) can also be set by an adjusting screw to give the desired vertical lift. The table has a 10 mm T-slot for attaching clamps. The lever bolt can be moved to give varying forces and different stroke lengths (see table).

Application:

For embossing, riveting, upsetting, and punching as well as for bending, compressing, and pressing in bushes etc.

Colour:

Light grey RAL 7035.

Note:

Hand lever presses with air support available in the online shop under No. 086761.

Technical description

Height without hand lever	500 mm
Stroke length long	0 - 45 mm

Table depth	170 mm
Stroke length short	0 - 23 mm
Installation height	75 - 240 mm
Force for long stroke	16 kN
T-slot to DIN 650	1 pc. size 10
Weight	32 kg
Footprint depth	310 mm
Throat	120 mm
Type	12
Footprint width	180 mm
Table width	200 mm
Mounting hole in the slide ram	10 H 7 mm
Force for short stroke	20 kN
Type of product	Toggle lever press