

Arbor press, Type: 3A



Order data

Order number	086790 3A
GTIN	2050001940438
Item class	08V

Description

Version:

Sturdy, hollow cast body of special cast iron with large base. Base with mounting holes for attaching to the support (workbench / subframe No. 086795). Rack and pinion slide ram of wear-resistant steel for the heaviest duties. Precise operation due to hardened and polished rack and pinion slide ram with long guides. Rotating table with four different recesses for the support of different workpieces. Slide ram actuation by lever arm.

Application:

For pressing in and pressing out sleeves, ball bearings, arbors, pins, bolts etc. Also for broaching work as well as use of simple cutting and stamping tools.

Colour:

Light grey RAL 7035.

maximum pressure delivery: 8.95 kN

Slide bar Ø: 48 mm

Throat to slide ram centre: 230 mm

maximum slide ram stroke: 400 mm

Cast body height: 700 mm

for workpiece Ø up to: 450 mm

Technical description

Cast body height	700 mm
Slide bar Ø	48 mm
Weight	92 kg
for workpiece Ø up to	450 mm
Slit width of the support table	25/45/65/85 mm
Footprint depth	480 mm
maximum slide ram stroke	400 mm
maximum pressure delivery	8.95 kN
Type	3A
Footprint width	250 mm
Throat to slide ram centre	230 mm
Type of product	Arbor press

Accessories

Stand for arbor press	086795
-----------------------	--------