

Arbor press, Type: 2



Order data

| | |
|--------------|---------------|
| Order number | 086790 2 |
| GTIN | 2050001940421 |
| Item class | 08V |

Description

Version:

Sturdy, hollow cast body of special cast iron with large base. Base with mounting holes for attaching to the support (workbench / subframe No. 086795). Rack and pinion slide ram of wear-resistant steel for the heaviest duties. Precise operation due to hardened and polished rack and pinion slide ram with long guides. Rotating table with four different recesses for the support of different workpieces. Slide ram actuation by lever arm.

Application:

For pressing in and pressing out sleeves, ball bearings, arbors, pins, bolts etc. Also for broaching work as well as use of simple cutting and stamping tools.

Colour:

Light grey RAL 7035.

maximum pressure delivery: 8.1 kN

Slide bar Ø: 42 mm

Throat to slide ram centre: 164 mm

maximum slide ram stroke: 300 mm

Cast body height: 545 mm

for workpiece Ø up to: 320 mm

Technical description

Data sheet

| | |
|---------------------------------|----------------|
| Type | 2 |
| for workpiece Ø up to | 320 mm |
| maximum slide ram stroke | 300 mm |
| Slit width of the support table | 15/25/35/50 mm |
| Weight | 45 kg |
| Slide bar Ø | 42 mm |
| maximum pressure delivery | 8.1 kN |
| Footprint depth | 358 mm |
| Cast body height | 545 mm |
| Throat to slide ram centre | 164 mm |
| Footprint width | 198 mm |
| Type of product | Arbor press |

Accessories

| | |
|-----------------------|--------|
| Stand for arbor press | 086795 |
|-----------------------|--------|