

**GECHTER****Hand lever toggle press, Type: 2,5****Order data**

Order number	086760 2,5
GTIN	2050000997099
Item class	08V

**Description****Version:**

Sturdy, hollow cast body with large base. Base with 4 holes for attachment to workbench etc. The press tool carriage runs without play on dovetail guides and is adjustable for height. Additionally the press stroke (ram stroke) can also be set by an adjusting screw to give the desired vertical lift. The table has a 10 mm T-slot for attaching clamps.

**Application:**

For embossing, riveting, upsetting, and punching as well as for bending, compressing, and pressing in bushes etc.

**Colour:**

Light grey RAL 7035.

**Note:**

Hand lever presses with air support available in the online shop under No. 086761.

Force for short stroke: 8 kN

Stroke length long: 0 - 42 mm

Throat: 90 mm

Installation height: 70 - 190 mm

Mounting hole in the slide ram: 10 H 7 mm

Table width: 150 mm

## Technical description

Footprint width	150 mm
Table width	150 mm
Installation height	70 - 190 mm
Force for short stroke	8 kN
Stroke length long	0 - 42 mm
Table depth	100 mm
T-slot to DIN 650	1 pc. size 10
Mounting hole in the slide ram	10 H 7 mm
Height without hand lever	320 mm
Footprint depth	200 mm
Weight	11.5 kg
Throat	90 mm
Type	2.5
Type of product	Toggle lever press