



Digital XT internal micrometer set, Measuring range: 6-10mm



Order data

Order number	428652 6-10
GTIN	5051102209650
Item class	46B

Description

Version:

3-point internal micrometer series for blind hole measurement from size 12.5 -16. Fixed carbide measuring jaws, from size 12.5 with carbide inserts. Large, sharp contrast digital display. Measuring spindle through-hardened and ground. Reliable measurement without a vernier. Compatible with the optional HCT (Hoffmann Group Connected Tools) app. Available free of charge for Android and iOS.

Function:

- **mm / inch selection.**
- **Setting 4 preset values.**
- **On / Off data storage button.**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Digital internal micrometers No. 428602 and setting rings with UKAS test certificate.

Optional extras:

Data cable No. 498948.

USB dongle No. 498952.

Setting rings No. 484030.

Extensions No. 428510.

Spare part:

Spare measuring heads No. 428605, measuring jaws No. 428745, return springs No. 428746.

Technical description

Measuring range	6 - 10 mm
Setting ring Ø	8 mm
Number of setting rings	1
Number of measuring heads	2
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Series	HCT
IP Index of Protection	IP 67
Power supply	Battery-powered
Wireless application	HID (Human Interface Device)
Wireless application	Manufacturer's software
Wireless application	HCT Mobile App
Standard	DIN 863
Reversible reading	mm / inch
Interface	USB interface
Interface	RS232C interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 6-10 mm	020550 6-10
--	-------------

Accessories

Connection cable Type USB2	498948 USB2
Connection cable Type R2	498948 R2
Replacement XT measuring head Measuring range 6-8 mm	428605 6-8
Bluetooth radio receiver for Bowers Type	498952
Digital XT internal micrometer Measuring range 6-8 mm	428602 6-8
Replacement XT measuring head Measuring range 8-10 mm	428605 8-10
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ringDIN 2250 C Nominal size Ø 7 mm	484030 7
Digital XT internal micrometer Measuring range 8-10 mm	428602 8-10
Setting ringDIN 2250 C Nominal size Ø 9 mm	484030 9
Measuring jaws set3 pieces Measuring range 6-8 mm	428745 6-8
Return spring set3 pieces Measuring range 6-8 mm	428746 6-8
Measuring jaws set3 pieces Measuring range 8-10 mm	428745 8-10
Return spring set3 pieces Measuring range 8-10 mm	428746 8-10