



Socket, 1/2 inch for Torx®, Torx® profile: E12



Order data

| | |
|--------------|---------------|
| Order number | 642700 E12 |
| GTIN | 4018754007271 |
| Item class | 63A |

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners. Nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Technical description

| | |
|--------------------|-----------------------------|
| Torx® profile | E12 |
| Length | 38 mm |
| Ø drive output end | 14.9 mm |
| Profile size A | 11.1 mm |
| Square drive | 1/2 in |
| Drive profile | Socket for TORX® screws |
| Material | Chrome alloy steel |
| Surface | chromium-plated over nickel |

Type of product

Socket insert