



Double-ended ring spanner, deeply cranked, phosphated, Width across flats: 18X19mm



Order data

Order number	615900 18X19
GTIN	4045197385475
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

Width across flats 2	19 mm
Width across flats 1	18 mm
maximum ring $\varnothing D_1$ max	28 mm
Spanner length L	290 mm
maximum ring $\varnothing D_2$ max	29 mm
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

