



Double-ended ring spanner set, deeply cranked, phosphated, Number of keys: 12



Order data

Order number	615910 12
GTIN	4045197385635
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

HOLEX – Chrome vanadium steel, phosphated.

Supplied with:

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6x7; 8x9; 10x11; 12x13; 14x15; 16x17; 18x19; 20x22; 21x23; 24x26; 27x32; 30x34

Technical description

Number of keys	12
Width across flats	metric
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated

Product name attribute	phosphated
Type of product	Spanner

Accessories

Double-ended ring spanner, deeply cranked Width across flats 27X32 mm	615900 27X32
Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615900 8X9
Double-ended ring spanner, deeply cranked Width across flats 20X22 mm	615900 20X22
Double-ended ring spanner, deeply cranked Width across flats 24X26 mm	615900 24X26
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615900 10X11
Double-ended ring spanner, deeply cranked Width across flats 21X23 mm	615900 21X23
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615900 14X15
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615900 6X7
Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615900 16X17
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615900 12X13
Double-ended ring spanner, deeply cranked Width across flats 30X34 mm	615900 30X34
Double-ended ring spanner, deeply cranked Width across flats 18X19 mm	615900 18X19