

Garant GRIDLINE

## ToolCar roller cabinet, 20×16G, Number of drawers: 6



### Order data

Order number	914520 6
GTIN	4045197892096
Item class	9GT

### Description

#### Version:

The ToolCar roller cabinet with scratch resistant, anti-slip and extremely surface-friendly **GARANT GridLine mat**. Easy exchange of the tray with other worktops (for example, bamboo) or with a bamboo worktop with vice. Valuable cupboard / side cupboard can be locked centrally together with drawers. Drawer fronts and cabinet stiles are clad with LDPE bumpers. In the event of collisions they reduce the damage to vulnerable surfaces and tools.

#### Fitted with:

Drawer front height: 75; 75; 75; 125; 200; 200 mm

#### Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

#### Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

#### Note:

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75; size 125 and size 200;

Slotted dividers No. 951510 size 75; size 125 and size 200;  
 Divider inserts No. 951721 – 951821 size 75; No. 951731 – 951821 size 125 and No. 951741 – 951821 size 200.

## Technical description

Number of drawers	6
Width	800 mm
Drawer usable depth	400 mm
Weight	78 kg
Height	1000 mm
Depth	500 mm
Drawer usable width	500 mm
Drawer usable width in G	20
Drawer usable depth in G	16
Series	ToolCar roller cabinet
Series	ToolCar
Individual drawer release system	One-hand
Drawer usable area in G	20×16
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Drawer usable width × usable depth in G	20×16G
Cylinder lock	modular lock barrel
Type of product	Roller cabinet

## Accessories

Slotted dividers Depth 16G suitable for drawer front height 75 mm	951510 75
---	-----------

Slotted dividersDepth 16G suitable for drawer front height  
125 mm

951510 125

Set of wheels for roller cabinets and mobile workbenches  
Type G

915567 G

Lock plate for GridLine Type VA21

914227 VA21