

Garant GRIDLINE

ToolCar roller cabinet, 20×16G, Number of drawers: 5



Order data

Order number	914520 5
GTIN	4045197892089
Item class	9GT

Description

Version:

The ToolCar roller cabinet with scratch resistant, anti-slip and extremely surface-friendly **GARANT GridLine mat**. Easy exchange of the tray with other worktops (for example, bamboo) or with a bamboo worktop with vice. Valuable cupboard / side cupboard can be locked centrally together with drawers. Drawer fronts and cabinet stiles are clad with LDPE bumpers. In the event of collisions they reduce the damage to vulnerable surfaces and tools.

Fitted with:

Drawer front height: 75; 75; 200; 200; 200 mm

Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Note:

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75 and size 200;

Slotted dividers No. 951510 size 75 and size 200;
 Divider inserts width No. 951721 – 951821 size 75 and No. 951741 – 951821 size 200.
 Cylinder lock: modular lock barrel
 Individual drawer release system: One-hand
 Drawer usable area in G: 20×16
 Height: 1000 mm
 Width: 800 mm
 Depth: 500 mm
 Drawer usable width: 500 mm
 Drawer usable depth: 400 mm
 Drawer usable width in G: 20

Technical description

Width	800 mm
Depth	500 mm
Height	1000 mm
Drawer usable width	500 mm
Weight	74.4 kg
Drawer usable depth	400 mm
Number of drawers	5
Drawer usable width in G	20
Drawer usable depth in G	16
Series	ToolCar roller cabinet
Series	ToolCar
Individual drawer release system	One-hand
Drawer usable area in G	20×16
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Drawer usable width × usable depth in G	20×16G
Cylinder lock	modular lock barrel
Type of product	Roller cabinet

Accessories

Slotted dividers Depth 16G suitable for drawer front height 75 mm	951510 75
Slotted dividers Depth 16G suitable for drawer front height 125 mm	951510 125
Set of wheels for roller cabinets and mobile workbenches Type G	915567 G
Lock plate for GridLine Type VA21	914227 VA21