

Garant GRIDLINE

**ToolCar roller cabinet with ComfortClose, 20×16G, Number of drawers: 6****Order data**

|              |               |
|--------------|---------------|
| Order number | 914524 6      |
| GTIN         | 4045197892140 |
| Item class   | 9GT           |

**Description****Version:**

The ToolCar roller cabinet with scratch resistant, anti-slip and extremely surface-friendly **GARANT GridLine mat**. Easy exchange of the tray with other worktops (for example, bamboo) or with a bamboo worktop with vice. Valuable cupboard / side cupboard can be locked centrally together with drawers. Drawer fronts and cabinet stiles are clad with LDPE bumpers. In the event of collisions they reduce the damage to vulnerable surfaces and tools.

**GARANT ComfortClose.** Self-closing drawers with damping.

**Fitted with:**

Drawer front height: 75; 75; 75; 125; 200; 200 mm

**Supplied with:**

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

**Colour:**

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

**Note:**

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75; size 125 and size 200;

Slotted dividers No. 951510 size 75; size 125 and size 200;

Divider inserts No. 951721 – 951821 size 75; No. 951731 – 951821 size 125 and No. 951741 – 951821 size 200.

## Technical description

|  |                        |
|--|------------------------|
| Drawer usable depth                              | 400 mm                 |
| Width  | 800 mm                 |
| Height   | 1000 mm                |
| Drawer usable width                              | 500 mm                 |
| Weight   | 78 kg                  |
| Number of drawers                                | 6                      |
| Depth  | 500 mm                 |
| Drawer usable width in G                         | 20                     |
| Drawer usable depth in G                         | 16                     |
| Series   | ToolCar roller cabinet |
| Series   | ToolCar                |
| Individual drawer release system                 | One-hand               |
| Drawer usable area in G                          | 20×16                  |
| Drawer/pull-out shelf load capacity              | 30 kg                  |
| Drawer runner extension (partial/full extension) | 100 %                  |
| Drawer runner extension                          | Anti-tilt lock         |
| Hoffmann perforated panel grid interval          | 9×9 mm                 |
| Drawer usable width × usable depth in G          | 20×16G                 |
| Cylinder lock                                    | modular lock barrel    |
| Type of product                                  | Roller cabinet         |

## Accessories

951510 75

Slotted dividersDepth 16G suitable for drawer front height  
75 mm

Slotted dividersDepth 16G suitable for drawer front height  
125 mm

951510 125

Set of wheels for roller cabinets and mobile workbenches  
Type G

915567 G

Lock plate for GridLine Type VA21

914227 VA21