

Garant GRIDLINE

**Roller cabinet with full extension drawers, 20×16G, Number of drawers: 10****Order data**

Order number	914540 10
GTIN	4045197892225
Item class	9GT

**Description****Version:**

Roller cabinet with scratch-resistant non-slip X-ABS tray, does not damage surfaces. The tray can easily be swapped with other worktops (e.g. bamboo) or with a bamboo worktop with vice.

**Fitted with:**

Drawer front height: 10 × 75 mm

**Supplied with:**

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

**Colour:**

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

**Note:**

Optional valuables cupboard / side cupboard No. 914791 not integrated in the central locking of the roller cabinet, closed by a separate cylinder lock.

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75;

Slotted dividers No. 951510 size 75;

Divider inserts No. 951721 – 951821 size 75.

## Technical description

Number of drawers	10
Height	1000 mm
Drawer usable depth	400 mm
Depth	500 mm
Width	800 mm
Weight	86 kg
Drawer usable width	500 mm
Drawer usable width in G	20
Drawer usable depth in G	16
Individual drawer release system	One-hand
Drawer usable area in G	20×16
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Drawer usable width × usable depth in G	20×16G
Cylinder lock	modular lock barrel
Type of product	Roller cabinet

## Accessories

Slotted dividersDepth 16G suitable for drawer front height 75 mm	951510 75
Set of wheels for roller cabinets and mobile workbenches Type G	915567 G
Lock plate for GridLine Type VA21	914227 VA21