

Garant GRIDLINE

## ToolTruck mobile workbench with bamboo worktop, 20×16G, Number of drawers: 6



### Order data

Order number	914568 6
GTIN	4045197892287
Item class	9GT

### Description

#### Version:

The ToolTruck mobile workbench has a 25-mm thick **bamboo** worktop of (suitable for mounting a vice). Cupboard with **2 storage shelves** and door. **Cabinet stiles are clad with LDPE bumpers.**

**Central locking** locks the door of the cupboard and drawers at the same time.

#### Fitted with:

Drawer front height: 75; 75; 75; 125; 200; 200 mm

#### Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

#### Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

#### Note:

Optional storage shelf / side compartment No. 914791 not integrated into the ToolTruck central locking system, locked instead by a separate cylinder lock.

For drawers of height 200 mm, more suitable components now include slotted dividers No.

951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75; size 125 and size 200;

Slotted dividers No. 951510 size 75; size 125 and size 200;  
 Divider inserts No. 951721 – 951821 size 75; No. 951731 – 951821 size 125 and No. 951741 – 951821 size 200.

Cylinder lock: modular lock barrel

Individual drawer release system: One-hand

Drawer usable area in G: 20×16

Height: 1000 mm

Width: 1195 mm

Depth: 500 mm

Drawer usable width: 500 mm

Drawer usable depth: 400 mm

Drawer usable width in G: 20

## Technical description

Weight	97 kg
Height	1000 mm
Depth	500 mm
Drawer usable depth	400 mm
Width	1195 mm
Number of drawers	6
Drawer usable width	500 mm
Drawer usable width in G	20
Drawer usable depth in G	16
Drawer usable area in G	20×16
Series	ToolTruck mobile workbench
Individual drawer release system	One-hand
Configurator relevant	yes
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular lock barrel
Product name attribute	20×16G

Type of product	mobile workbench
-----------------	------------------

## Accessories

Electronics screwdriver set Number of tools 8	953386 8
Combination spanner set Number of tools 9	952325 9
Universal cordless screwdriver set Number of tools 62	955028 62
Workshop file set Number of tools 5	952210 5
Screwdriver set Number of tools 8	953415 8
Screwdriver set for Torx®, with T-handle Number of tools 8	953170 8
Non-slip mats set for drawers,5 pieces Dimension in G 20X16	951885 20X16
Screwdriver set Number of tools 8	953420 8
Pliers set, fully insulated Number of tools 3	954475 3
Workshop set Number of tools 23	955001 23
Measuring tools set Number of tools 7	952070 7
Screwdriver set Number of tools 5	953307 5
Workshop set Number of tools 36	955017 36
Tool organiser system setfor 3 drawers Type G1	955051 G1
Writing surface Type 1	914835 1
Perforated panelsingle-sided for ToolTruck Height 444 mm	914855 444
Screwdrivers with impact cap Number of tools 7	953423 7
Divider insertsWidth 4G suitable for drawer front height 75 mm	951741 75
Socket set 1/4 inch Number of tools 28	953624 28
Ribbed rubber mat for drawers Dimension in G 20X16	951910 20X16
Double open ended spanner set Number of tools 5	952385 5
Perforated panelsingle-sided for ToolTruck Height 222 mm	914855 222
Tweezers set Number of tools 5	954735 5

Waste bin Capacity 24 l	914940 24
Drawer Usable height 80 mm	914770 80
Screwdriver set for Torx® Number of tools 5	953062 5
Media tray Height 80 mm	914915 80
Perforated panel double-sided for ToolTruck Height 222 mm	914856 222
Hammer / taper pin punch / pin punch set Number of tools 15	954668 15
Valuables cupboard / side cupboard Type L	914791 L
Nut spinner set Number of tools 9	952725 9
Workshop set Number of tools 34	955003 34
Slotted edge partitions set, 2 pieces Depth 16G suitable for drawer front height 125 mm	951560 125
Perforated panel double-sided for ToolTruck Height 444 mm	914856 444
Hexagon ball-point screwdriver set Number of tools 6	952835 6
Mat for drawers Dimension in G 20X16	951830 20X16
Perforated panel double-sided for ToolTruck Height 950 mm	914856 950
Perforated panel single-sided for ToolTruck Height 950 mm	914855 950
Media tray Height 160 mm	914915 160
Double-ended ring spanner set Number of tools 6	952309 6
Screwdriver bits set Number of tools 69	954751 69
Slotted edge partitions set, 2 pieces Depth 16G suitable for drawer front height 75 mm	951560 75
Workshop set Number of tools 23	955013 23
Socket set 1/4 inch and 1/2 inch Number of tools 82	955025 82
Tray with anti-roll lip Type 1	914830 1
Slotted dividers Depth 16G suitable for drawer front height 75 mm	951510 75
Pliers set Number of tools 4	954075 4
Cable reel with automatic rewind Type DE	914890 DE

Socket set 3/8 inch Number of tools 13	953690 13
Workshop file set Number of tools 5	952205 5
Micrometer set Number of tools 4	952095 4
Slotted dividersDepth 16G suitable for drawer front height 125 mm	951510 125
Divider insertsWidth 4G suitable for drawer front height 125 mm	951741 125
Tool organiser system setfor 2 drawers Type H1	955061 H1
Screwdriver set Number of tools 6	953421 6
Pliers set Number of tools 3	954165 3
LED lamp for ToolTrucksupplied with support columns Type 20	914873 20
Storage shelffixed Type 1	914774 1
Workshop accessories assortment Number of tools 4	954730 4
Ladder holder Type 1	914945 1
Screwdriver set Number of tools 6	953325 6