

Garant GRIDLINE

Mobile workbench with 5 drawers, can be pulled out from either side, 20×16G, Number of drawers: 5



Order data

Order number	914582 5
GTIN	4045197892317
Item class	9GT

Description

Version:

The stable sheet metal housing of the mobile workbench contains 2 integral storage trays. The side wall is perforated for attachment of accessories. Drawer inner face smooth but nevertheless suitable for dividers. The drawers are unlocked by a central catch within the extruded handle. Drawers can be centrally locked by means of a **cylinder lock**. With roller bearing wheels (2 castors with parking brake, 2 fixed wheels). 25 mm thick **bamboo** work top, suitable for fitting a vice.

Fitted with:

Drawer front height: 75; 75; 125; 125; 200 mm

Supplied with:

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75,

each 125 mm drawer 1 slotted partition No. 951510 size 125.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite grey.

Note:

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951510 size 200, edge partitions No. 951560 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951560 size 75; size 125 and size 200;

Slotted dividers No. 951510 size 75; size 125 and size 200;
 Divider inserts No. 951721 – 951821 size 75; No. 951731 – 951821 size 125 and No. 951741 – 951821 size 200.

Cylinder lock: modular lock barrel

Drawer usable area in G: 20×16

Height: 900 mm

Width: 1000 mm

Depth: 525 mm

Drawer usable width: 500 mm

Drawer usable depth: 400 mm

Drawer usable width in G: 20

Technical description

Depth	525 mm
Drawer usable depth	400 mm
Drawer usable width	500 mm
Number of drawers	5
Weight	63.4 kg
Width	1000 mm
Height	900 mm
Drawer usable width in G	20
Drawer usable depth in G	16
Drawer usable area in G	20×16
Configurator relevant	yes
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	75 %
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular lock barrel
Product name attribute	20×16G
Type of product	mobile workbench

Accessories

Slotted dividers Depth 16G suitable for drawer front height
75 mm

951510 75

Slotted dividers Depth 16G suitable for drawer front height
125 mm

951510 125

Set of wheels for roller cabinets and mobile workbenches
Type G

915567 G