

**Cordless inspection camera, Manufacturer's designation: GIC120C****Order data**

| | |
|--------------|----------------|
| Order number | 492710 GIC120C |
| GTIN | 3165140817929 |
| Item class | 03B |

Description**Version:**

- **89 mm / 3.5 inch colour LCD display.**
- **Automatic rotation of the image ("Up is Up"™ function).**
- **Transmission of images and videos directly via microUSB cable or microSD card.**
- **Dual power source: Can be operated both with 12 V Li-ion battery, and also with standard alkaline batteries.**
- **Digital zoom for better detection of details.**
- **3-stage LED illumination for lighting dark places.**

Compact cordless inspection camera for visual inspection of places that are difficult to access.

Supplied with:

Supplied with 1 × 12 V / 2.0 Ah Li-ion battery, charger, 4 GB microSD card, camera cable No. 492716 size 1.2, micro-USB cable, hook, magnet, mirror, L-BOXX.

Technical description

| | |
|--------------------|------------|
| Display resolution | 320×240 px |
| Display size | 3.5 in |
| Battery voltage | 12 V |

| | |
|--|------------------------------|
| Camera head Ø | 8.5 mm |
| Length of the camera cable | 1200 mm |
| Battery capacity | 1.5 Ah |
| Weight | 0.64 kg |
| Manufacturer's designation | GIC 120 C |
| Power supply | Rechargeable battery-powered |
| suitable battery - supplier / battery type / voltage | Bosch 12 V |
| Packaging | Carrying case (L-Boxx) |
| Type of product | Endoscope |

Accessories

| | |
|--|------------|
| Camera cable with probe Cable length 3,0 m | 492716 3,0 |
| Camera cable with probe Cable length 1,2 m | 492716 1,2 |