



## Socket, 1/2 inch for Torx®, Torx® profile: E24



### Order data

Order number	642700 E24
GTIN	4018754007325
Item class	63A

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners. Nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

#### Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

### Technical description

Torx® profile	E24
Ø drive output end	27.8 mm
Profile size A	22.1 mm
Length	41.2 mm
Square drive	1/2 in
Drive profile	Socket for TORX® screws
Material	Chrome alloy steel
Surface	chromium-plated over nickel

Type of product

Socket insert