



## Cordless inspection camera, Manufacturer's designation: M12ICAV



### Order data

Order number	492712 M12ICAV
GTIN	4002395159994
Item class	03L

### Description

#### Version:

Compact cordless inspection camera for visual inspection of places that are difficult to access.

- **89 mm / 3.5 inch removable wireless colour LCD display.**
- **Audio, video and photo function, digital zoom of 100 – 400%.**
- **Automatic contrast compensation and white balance.**
- **Waterproof camera head with 3-step LED illumination.**
- **Flexible waterproof 274 cm long camera cable.**
- **Digital zoom for better detection of details.**

#### Supplied with:

Supplied with 1× 12 V / 2.0 Ah Li-ion battery, C12 C charger, 2740 mm cable, 8 GB SD card, carrying case.

### Technical description

Display size	3.5 in
Display resolution	320×240 px
Battery voltage	12 V

Manufacturer's designation	M12 ICAV3-9
Camera head Ø	12.4 mm
Battery capacity	2 Ah
Length of the camera cable	2740 mm
Weight	0.72 kg
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Carrying case
Type of product	Endoscope