

Interior brush NOVOFLEX-B SiC180 grit, Type: 7



Order data

| | |
|--------------|---------------|
| Order number | 574495 7 |
| GTIN | 4013349576996 |
| Item class | 57L |

Description

Version:

Self-centring interior brush with flexible bristles carrying **silicon carbide spheres**. Overall length 200 mm.

Application:

For **chamfering, finishing of surfaces** and **honing**. Generates **fine evenly ground surface** with high contact area. For use in power drills and fixed drills. Recommended speed 350 – 700 rpm, contact time 20 – 40 seconds.

Note:

Do not use dry, use with cutting oil No. 084205.

Technical description

| | |
|---------------------------------|-----------------------------|
| suitable for bore \varnothing | 6.1 - 7 mm |
| Brush $\varnothing D_1$ | 8 mm |
| Working length L_3 | 50 mm |
| Shank $\varnothing D_s$ | 3.6 mm |
| Series | NOVOFLEX-B |
| Brush material | Silicon carbide |
| Grinding medium code | SiC |
| Grit | 180 |
| recommended speed | 350 - 700 min ⁻¹ |
| Type of product | Internal brush |

Accessories

High-performance cutting oil free of mineral oilUV 80
Contents 20 l

084205 20

High-performance cutting oil free of mineral oilUV 80
Contents 5 l

084205 5

High-performance cutting oil free of mineral oilUV 80
Contents 0,25 l

084205 0,25