

Mitutoyo**Scale unit vertical, Measuring range: 150mm****Order data**

Order number	499402 150
GTIN	4946368128382
Item class	44A

Description**Version:**

With **absolute electronics** and large easy-to-read display digits. One-off setting of the zero position, which remains the absolute zero point until the battery has to be replaced (approx. 1.5 years). Maximum measuring precision with very high speed of travel. ZERO/ABS function – zero setting and changeover between relative and absolute measurement.

Scale unit with capacitive electronic measuring system. **For vertical installation.**

Application:

Suitable for measuring and positioning tasks on machine tools, jigs, etc.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497085.

Technical description

Overall length L ₂	270 mm
Calibration	Price on request
Length of the measuring beam L ₁	294 mm

Scale divisions	0.01 mm
Weight	280 g
Measuring range	0 - 150 mm
Error limit	0.03 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Type of product	Scale unit

Services

Calibration Universal caliper maximum measuring range 600 mm	021400 600
--	------------

Accessories

Multi-receiver / USB keyboard interface Type	498975
Connecting cable with data switch Type D2	497085 D2
Transmitter Type S11E	498966 S11E
Connecting cable with data switch Type USB2	497085 USB2
Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type D1	497085 D1
Button cell / special battery Battery type 357	081560 357